



Compact Ionizing Bar IN-LINE fusION™

Simco-lon's Compact Ionizing Bar In-Line fusION is an air ionizer capable of controlling electrostatic charge in the local area. Applications for In-Line fusION are those found inside process equipment and mini-environments in the semiconductor, flat panel display, pharmaceutical, and medical device industries. It is especially well suited for longer length delivery line applications.

In-Line fusION is easy to install, operate and maintain. Simply mount In-Line fusION in a convenient location adjacent to the static problem. Connect the power supply and static charge is eliminated. No adjustments are necessary with Simco-Ion's auto balancing technology. This incredibly compact ionizer offers either tungsten or ISO Class 1 cleanroom grade silicon carbide emitters. In-Line fusion is also ideal for system integration with remote alarm capability. Multiple units can be linked together from one 24 VDC power source allowing up to 5 units to be daisy-chained. In-Line fusION can be powered directly from a process tool's 24 VDC power source or by the Simco-Ion fusION power supply kit.

Features

- Delivers ions through long tubes
- Compact Design
- Visual ionizer status indicator and digital level remote alarm output
- Single power source for multiple fusION ionizers
- available

Benefits

- Convenient static control is previously inaccessible target locations
- Fits into the tight confines of any process tool
- Standard features for convenient user operation
- Daisy-chain, up to 5 fusIONs, perfect for layered in-tool ionization protection
- Optional air knife, air ring and N2 attachments Customize In-Line fusION for extremely tight areas and for clean environments

Specifications

In-line fusION			
Input Voltage	24 VDC, 0.075A		
Discharge	See table below		
Balance	<±50V		
Coverage Area	12" x 12" @ 6" spacing		
Air Supply	Clean Dry Air (CDA) or Nitrogen		
Airflow	0.8 scfm @ 5 psi to 3.6 scfm @ 50 psi		
In-Line Gas	1/4" OD, 1/8" ID insulative tubing		
Output Current	5 μΑ		
Operation Mode	Steady-state DC		
Emitters Points	Tungsten or Silicon Carbide		
Connectors	DC power IN/OUT: 4 position modular, 4-pin "handset type"		
LED Indicators	Green POWER ON; red FAULT (TTL level alarm output)		
Operating Env.	Temperature 15-50°C (59-122°F) recommended; relative humidity 20-65%		
Mounting	Integrated mounting flanges accept four (4), #4 or #6 screws		
Enclosure	White Polycarbonate		
Dimensions	2.5H x 1.5W x 4.5L in.(6.4 x 3.8 x 11.4 cm) includes air connectors		
Weight	0.3 lb (136 g)		
Warranty	Two year limited warranty		
Certifications	RoHS Compliant (🧲 230V, 50 Hz c 🕼 us 120V, 60 Hz		
Power Supply			
Output Voltage	24 VDC		
Input Voltage	100-240 VAC, 50/60 Hz		

Weight	11 oz (318g)
Dimensions	1.3H x 2.0W x 3.5L in. (3.3 x 5.1 x 8.9 cm)

Discharge Time Performance

	0.14" - Single Output Tube (inside diameter)					
Tube Length	30 PSI	15 PSI	5 PSI	2 PSI		
6"Tube	0.5 sec	0.8 sec	1.4 sec	2.5 sec		
12"Tube	0.8 sec	1.4 sec	2.2 sec	4.0 sec		
18"Tube	1.0 sec	2.1 sec	3.5 sec	6.2 sec		
24"Tube	1.8 sec	3.2 sec	5.2 sec	9.6 sec		
36" Tube	6.0 sec	6.8 sec	10 sec	18 sec		
48" Tube	9.5 sec	13 sec	22 sec	40 sec		

Offset voltage and discharge time determined as per ANSI/ESD STM3.1 ionization using a 6"x 6", 20 pF plate (charge plate monitor). Discharge times are in seconds from 1000-100V.

Ordering Information

4012228	fusION In-Line, Silicon Carbide (SiC) emitters
4012229	fusION In-Line, Tungsten (W) emitters
4010448	fusION Power Supply Kit, 120V, 60 Hz, NA/Japan
4010449	fusION Power Supply Kit, 230V, 50 Hz, EU
4010450	fusION Power Supply Kit, 230V, 50 Hz, UK
5051530	fusION In-Line Kit, 6" Air Knife Rod
5051538	fusION In-Line Kit, 12" Air Knife Rod
5051535	fusION In-Line Kit, 6" Air Ring
5051539	fusION In-Line Kit, 12" Air Ring
5051513	fusION In-Line Nitrogen N2 Kit

In-line fusION Ionizer

For the longest time, end-users of ionization devices have desired the ability to deliver the ions through a lengthy tube that would allow them to bring focused ionized air conveniently to their target without being attracted to grounded metal components in their environment and without having to bring the ion generation source close to their target.

Simco-lon has developed a DC in-line ionizer that has the ability to provide fast decay times through output tubes up to six feet in length. Since the ion-to-ion recombination down the output tube is so limited, the single output tube has the ability to be split into multiple tubes each with excellent performance allowing the fusION ionization source to service multiple locations from a single ionization source. This unit comes equipped for use with clean dry air (CDA); however, a Nitrogen (N2) kit is available.



Air Ring Output Application



Air Knife Output Application



Nitrogen (N2) Kit



DS-In-line Fusion 5201069_V1 - 08/12 © 2012 Simco-Ion All rights reserved.

Simco-lon

Technology Group 1750 North Loop Rd., Ste 100 Alameda, CA 94502 Tel: 800.367.2452 (in USA) Tel: 510.217.0600 info@simco-ion.com www.simco-ion.com